



Electrician's test leads

- High quality electrical test leads
- Standard or fused test leads
- Lock-on crocodile clips
- Includes crocodile clips and probes
- Double insulated
- Meets safety requirements IEC 61010-2
- GS38 compliant

New Megger professional test leads

Megger now offer a range of general purpose test leads developed for the contracting electrician. Fitted with 4mm, right-angled shrouded connectors, these test leads are available in either standard or fused options and incorporate several features requested by customers who have been frustrated with their current leads.

Colour options are Red/Black or Red/Green for the un-fused leads. Fused leads are available in Red/Black only.

All test lead kits are supplied with test prods and heavy-duty push-on crocodile clips as standard. Crocodile clips are simply onto the test probes and have a locking ring ensures the crocodile clips cannot come off accidentally.

All test leads are rated to CATIII 1000V. By fitting the Crocodile clips the leads are automatically rated to CATIII 600V.

All test lead sets are 1.25 metres long and


Standard test leads

- Comfortable contoured rubber finger grips
- Heavy duty push-lock crocodile clips
- Transparent removable probe tip covers
- GS38 probe tips (<4mm exposed tip)
- o Right angled test plugs
- o Highly flexible PVC cable
- o Round finger guard for safe finger location
- Double insulated leads with white inner for easy damage location.
- 10amp rated current capacity.
- CATIII 1000V test leads and probes
- o CATIII 600V (CATII 1000V) crocodile clips
- CE approved

Available as Red/Black or Red/Green test leads

Fused test leads

- o Conforms fully with GS38 test lead requirements
- As the standard test leads but fused with 500mA 50Kv HSB





Available in Red/Black only

All leads are manufactured to Megger's exacting standards and fully conform to IEC1010-2 requirements.

ORDERING INFORMATION		
Item (Qty)	Included Accessories	Order Code
Standard Red/Black test leads (Right Angled)	Crocodile clips and probe tip shrouds	6220-779
Standard Red/Green test leads (Right Angled)	Crocodile clips and probe tip shrouds	6220-784
Fused Red/Black test leads (Right Angled)	Crocodile clips and probe tip shrouds	6220-789
IINITED KINGDOM IINITED STATES		

UNITED KINGDOM
ARCHCLIFFE ROAD, DOVER, KENT CT17 9EN
ENGLAND
PHONE: +44 (0) 1304 502100/202620
FAX: +44 (0) 1304 502300/207342
EMAIL: avosales.dover@avointl.com

UNITED STATES 4271 BRONZE WAY DALLAS, TX 75237-1017 USA PHONE: (214) 330-3255 FAX: (214) 333-3533 EXPORT FAX: (214) 337-3038

