


Frame-type 5 plug-in units 3/6 U kits

Print page






- Right and left extruded side panels with grooves for sliding in printed board (standard card position only on the left)
- Assembly of further printed boards via assembly of guide rails in the perforated covers
- Front panel EMC shielded, covers with perforation





Item	Description			
1	1	Front panel, Al, 2.5 mm, front anodised, rear colourless chromated		
2	1	Handle, grey, PPE, UL 04 V-1		
3a	1	Rear panel, Al, 1.5 mm, with cut-out for one connector		
4	2	Side panel, Al extrusion, with groove for one printed board		
5	2	Cover, perforated, Al, 1 mm		
6	2	EMC contact strips, stainless steel		
7	1	Assembly kit		



Technical data:

Height	Width	Description	Description
3 U		T = 227 mm front panel, shielded	Rear panel with cut-out for 1 connector

Technical data:

T = plug-in unit side panel depth

Further Information:

