



210



- High protection rating IP 65
- B 15 d socket integrated in the base
- Safe CAGE CLAMP® technology
- Small shape with high dome
- Optimum illumination
- Available for base or bracket mounting
- Connection without the need to disassemble the product

TECHNICAL SPECIFICATIONS:

Housing:	PA 6.6 GF, black
Dome:	Polycarbonate, transparent
Connection:	CAGE CLAMP® technology up to 2,5mm ² max. Contact protection according to VDE

	210	213
Fixing:	Base mounting with flat seal	Bracket mounting, including cable gland M 12 x 1,5
Dimensions (Diameter x Height):	57 mm x 82 mm	57 mm x 82 mm
Weight:	55 g	61 g
Operating voltage:	max. 250 V	max. 250 V
Bulb socket:	B 15 d, 10 Watt max.	B 15 d, 10 Watt max.
Bulb change:	via removal of dome	via removal of dome
Bulbs not included in assembly		

210 Permanent/LED/Flashing Beacon

