




0705 STRAIN-RELIEF BUSHING



Chassis Thickness


- Material: UL approved Nylon 66, 94V-2 (Black)
 - Cust assembly cost, prolongs cord life.
- Used extensively for protecting cords of computer, apparatus...etc.



CORD ASSEMBLY

Item No.	Cross Section Shape	Wires Accomodate		Mounting Hole		Part L D	Max. Chassis Thickness F	Packing
		U.L. Wire	Size	A	B			
SR-F21	FLAT	SPT-1	2.3×4.5	9.5	8.7	10.3	0.5~1.6	1000pcs
SR-F23			2.8×5.3					
SR-F31		SPT-1	3.0×5.6	11.0	9.9	10.3	1.0~1.6	
SR-F32		SPT-1 SP×1	3.0×5.6	11.0	9.9	10.3	1.9~2.5	
SR-F41		SPT-218/2, 16/2	3.0×7.1	12.7	11.8	10.3	0.5~1.6	
SR-F42			3.8×7.6					
SR-F51		SPT-2	3.0×7.1	12.7	11.8	10.3	1.8~2.5	
SR-F53		SPT-3	3.8×7.6					
SR-F51		SPT-3	5×10.4	14.3	13.2	15.2	0.5~1.6	
SR-F53		SPT-3	5×10.4	13.2	13.0	15.2	1.8~3.5	
SR-5R1	581 902	SVI, SVT	6.2φ-7.4φ	12.7	11.5	11.0	0.5~1.6	
SR-5R2	581 914	SVI, SVT	6.2φ-7.4φ	12.7	11.5	11.0	1.8~2.5	
SR-6W2	581 926	SVI, SVT	7.6φ	12.7	11.8	11.0	1.8~2.3	
SR-6P1	ROUND 938	SJC3C#18	7.4φ-8.2φ	15.9	14.0	14.8	0.5~1.6	
SR-6P3	SJD 18/3, 16/2 16/3, 18/4 940	SJC3C#18	7.4φ-8.2φ	15.9	14.0	14.8	1.9~3.2	
SR-6R1	581 951	SJ,SJT,3C#16	8.2φ-9.2φ	15.9	14.0	14.8	0.5~1.6	
SR-6R3	963	SJ, SJT,3C#16	8.2φ-9.2φ	15.9	14.0	14.8	1.9~3.2	
SR-7R1		SJT,3C#14	9.2φ-10.5φ	19.0	16.5	19.0	0.5~1.6	
SR-7R3			11φ	19.8				
SR-8R3		SJT,3C#14	9.2φ-10.5φ	19.0	16.5	19.0	1.9~3.2	
SR-8R3			11φ	19.8				
SR-9R1		20~30PCS#18	11φ-15φ	19.0	19.0	17.5	0.5~1.6	
SR-9R7			SJT,3C#10	15.2φ-16.3φ	28.0	25.5	25.2	1.0~7.2
SR-9R7				17.5φ	30.2			

0705A STRAIN RELIEF BUSHING ASSEMBLY TOOL



Item No. : KT-1 (STAINLESS)

- | | | | | |
|---------------------|--------|--------|--------|--------|
| Applicable Bushings | SR-F21 | SR-F23 | SR-F31 | SR-F32 |
| | SR-F41 | SR-F42 | SR-F51 | SR-F53 |
| | SR-5R1 | SR-5R2 | SR-6W2 | SR-6P1 |
| | SR-6P3 | SR-6R1 | SR-6R3 | SR-7R1 |
| | SR-7R3 | SR-8R3 | SR-9R7 | |