
AUDIO CONNECTORS



A range of low cost professional quality plugs and sockets moulded from tough nylon. Metal fittings are silver plated brass

SOCKETS may be mounted to front or rear of chassis Rear mounting may utilise direct PCB mounting, using PC versions


To facilitate soldering - rear of contact pins are hollow When making a large number of connections to a pin, heat sinking - by using a metal plug - is advised Socket ACF has panel air-tight construction

SPECIAL VARIANTS (refer to Office for details) ACM R/PC, ACFR/PC Space saving version with PC pins at 90° to std version

Versions to accept M3 selftap screws in mounting holes - put prefex 'X' in front of part No eg XACMR

PLUGS APM, APF incorporate integral cable clamp/ strain relief. These may be colour coded for identification

PART NUMBERS (STD MODELS) ACM - CP3000, ACF - CP3001 ACM - PC, - CP30005, ACF - PC, - CP30015 PLUG APF - CP3003, PLUG APM - CP3004



TECHNICAL DATA

CURRENT RATING CONTACT RESISTANCE INSULATION BREAKDOWN 1600 VAC between contacts

3 pin 16 amp/250 VAC Less than 3m ohms (new) and housing

MATERIALS

SHELL PINS CONTACT PLATING

Glass filled nylon Brass 5um silver over 5um of nickel

CLIFF LOW NOISE METAL RANGE - SEE OVER