


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/22/08	D.GRIFFIN
B	ECN 3677: DELETED NOTE 1	11/14/08	D.CASTRO
C	ECN5151: UPDATED FORMAT. CHANGED LENGTH DIM LOCATION.	11/17/10	DFP
D	ECN 5268: ADDED LABEL WITH L-COM P/N TO NOTE 2	1/21/11	D. CASTRO

"J1"
**SERIAL ATA RECEPTACLE,
 7 PIN CONNECTOR,
 STRAIGHT, W/ LATCH,
 OVERMOLDED, COLOR: BLACK**



"J2"
**SERIAL ATA RECEPTACLE,
 7 PIN CONNECTOR,
 RIGHT ANGLE, W/ LATCH,
 OVERMOLDED, COLOR: BLACK**

**CABLE: UL21149 SERIAL ATA 26 AWG,
 JACKET: PVC, COLOR: RED**



WIRING DIAGRAM

PART #	LENGTH	
	INCHES	MLLIMETERS
CASATARL-8	8	203.2
CASATARL-12	12	304.8
CASATARL-16	16	406.4
CASATARL-18	18	457.2
CASATARL-24	24	609.6
CASATARL-36	36	914.4

NOTE:

1. EACH CABLE ASSEMBLY SHALL BE SUBJECTED TO A CONTINUITY TEST.
2. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG AND LABELED WITH L-COM PART NUMBER.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY E. STAUBLE	7/17/08		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	7/21/08	PRODUCT DESCRIPTION CBL,SATA W/LATCH STR/RA	
	APPROVED BY S. SMITH	7/21/08		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CASATARL-X
		SCALE: NONE	CAD FILE: CASATARL-X.SLDDRW	SHEET 1 OF 1