


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/05/04	MCCORMICK
B	ECN# 2731 - ADDED ROHS STAMP	10/23/07	D.GRIFFIN
C	ECN 4278: ADDED OPERATING TEMPERATURE RANGE AND PACKAGING	9/30/09	D.FRISIELLO



RoHS Compliant ✓

- NOTES:**
1. IP (INGRESS PROTECTION) RATING: 67.
  2. OPERATING TEMPERATURE RANGE: -40° C TO +105° C.
  3. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.03 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	02/05/2004			
	CHECKED BY D.PARHAM	02/05/2004	CATEGORY DATA CABLING		
	APPROVED BY R.CARRICK	02/05/2004	PRODUCT DESCRIPTION DB9 MALE WATERPROOF SOLDER		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. WPSD9P	REV. <b>C</b>
REF	SCALE: NONE	CAD FILE: WPSD9P.SLDDRW	SHEET 1 OF 1		