



(09 WAY CONNECTOR)

(15, 25 & 37 WAY CONNECTOR)

FEMALE JACK SCREW

No. of Ways	*Male Jack Screw	Female Jack Screw	A	B	C	D	E ±0.1	F	G
09	MD 09T	MD 09TF	31.4	—	14.5	24.0	25.0	32.0	7.9
15	MD 15T	MD 15TF	42.0	28.5	14.3	30.0	33.3	38.0	10.0
25	MD 25T	MD 25TF	55.5	41.9	25.1	36.0	47.0	44.0	14.2
37	MD 37T	MD 37TF	69.8	57.5	39.2	38.0	63.5	46.0	18.0

\* Add suffix '3' for male jack screw with M3 threads e.g. MD 09T3.

**Characteristics:**

- \* Male/Female Jack Screw having 4–40 UNC threads.
- \* External cable clamp, top cable entry.

**Material:**

Hood: ABS (metallised).  
Screws: Steel, Zinc plated.

ISS.	DATE	MODIFICATION	SIGN.
1	19.03.05		

TOLERANCES  
UNLESS  
OTHERWISE  
SPECIFIED  
±0.1

METALLISED PLASTIC TOP  
CABLE ENTRY HOOD

DIMENSIONS IN MM		
	DATE	SIGN.
DESIGN	19.03.05	
DRAWN	19.03.05	
CHKD.		
APPD.		
DRG. NO.		
DHDCU-004. A4.		
SHEET 1 OF 1		

SCALE ~

