


D

C

B

A



RP78601

RP78602

PART NO:	PART NAME:	MATERIAL/SURFACE:	OPTIONAL DESCRIPTION
----------	------------	-------------------	----------------------

PART LIST

TOLERANCES UNLESS OTHERWISE SPECIFIED ACCORDING TO ISO 8015 and ISO 2768-m

DIMENSIONS: mm

test dimen. / Prüfmaß:  $\square$ ; auxiliary dimen. / Hilfsmaß: ( ) ; theor. dimen. / theor. Maß:  $\square$  ;  
 production control dimen. / Fertigungskontr.maß: [ ] ; dimen. for measure. technology / messtechn. rel. Maß: [ ] ;

				DEPARTMENT		
				DRAWER	25.09.2007	hel
				CHECKED	25.09.2007	hel
<b>ECO-11-005027</b>	<b>19APR11</b>	<b>HMR</b>		APPROVED	25.09.2007	mader
ECO-NO.:	DATE	NAME	INFO		DATE	NAME



SCALE:	NAME:	DWG NO.:
-	RT Print-Socket	1393234

REPLACEMENT FOR:	DWG LOC NO.:	IF	SHEET:	OF	REVISION:	A2	A 4
------------------	--------------	----	--------	----	-----------	----	-----

OPTIONAL NO.:  
**RP78601--/01**