

5

4

3

2

1

DRAWING NO.
28-90027

REVISIONS


01	OFFICIAL RELEASE				2009.09.0
	08-18-09	L	L	T H	Betty 09.38.26 08.00

Description: CP785 75 OHM BNC(M) 1PC CR RG6
 Part No: 28-90027
 Application: For RG 6 Cable
 Crimp Tool: N/A
 Impedance: 75 ohm
 Frequency Range: 0~2 GHz
 Material: Body Brass Nickel plated
 Insulator TPX
 Contact Brass Gold plated
 Sleeve Brass Nickel plated
 Coupling nut Zinc Nickel plated
 RoHS Compliance: Yes
 Technical Detail: Refer to Emerson Document P/N 27-0000



受控 CONTROLLED DOCUMENT

编号 P/N	28-90027-C UST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	----------------	-----------	----	------------------	-----------



CUSTOMER COPY

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY LINDA.WU	DATE 08-18-09
DECIMALS	mm	CHECKED BY LINDA.WU	DATE 08-18-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-18-09
X.X	± 0.3	U/M	mm
X.XX	± 0.1		
ANGLES	$\pm 0.5^\circ$		

	Connectivity Solutions	
	TITLE CP785 75OHM BNC (M) 2PC CR RG6	

SHEET 1 OF 1	DRAWING NO. 28-90027	SIZE A
-----------------	-------------------------	-----------

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1