

5 4 3 2 1

受控 CONTROLLED DOCUMENT

编号 P/N	CPMC8813-CUST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	---------------	-----------	----	------------------	-----------

DRAWING NO.
CPMC8813-CUST

REVISIONS

OFFICAL RELEASE				
01				
08-17-09	J	T	T	

Betty 20090908
20080510
+0800

D
C
B
A

D
C
B
A

Description: BNC 3pc crimp plug RG223

Part No: CPMC8813

Application: For RG142,223,400,55 Cable

Crimp Tool: 24-9958P

Impedance: 50 Ohms

Frequency Range: 0-4 GHz

Material:

- Body Zinc Nickel plated
- Contact Brass Gold plated
- Insulator Teflon
- Crimp sleeve Brass Nickel plated
- Coupling nut Zinc Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000

DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	JEAN.JIN	08-17-09
X	± 0.5	CHECKED BY	DATE
X.X	± 0.2	TERRY.W	08-17-09
X.XX	± 0.1	APPROVED BY	DATE
ANGLES	± 0.5°	THOMAS	08-17-09
		U/M	mm

<p>Connectivity Solutions</p>		
		TITLE
BNC 3PC CRIMP PLUG RG223		
SHEET	DRAWING NO.	SIZE
1 OF 1	CPMC8813-CUST	A

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5 4 3 2 1