




A	1	2	3	4	5	6	7	8
REV ZONE	ECO	DESCRIPTION	DATE	BY	APPR			
A1	--	RELEASE NUMBER	02/09/12	--	--			
A2	--	CHANGE NOTES	19/02/13	JARRY	--			



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen
受控文件
2013年2月25日



- 注(NOTES):
- 材料 Material:
绝缘体: 热塑性塑料, UL 94V-0;
Insert: thermoplastic, UL 94V-0;
颜色: ATP06-2S=灰色, ATP06-2S-BLK=黑色
Color: ATP06-2S=Gray, ATP06-2S-BLK=Black
 - 工作温度 Operation temperature: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$;
 - 性能参数 Specification:
 - 额定电压 Rating Voltage: 250VAC MAX;
 - 额定电流 Rating current: 25A;
 - 耐压 Withstanding voltage: 1500VAC;
 - 绝缘电阻 Insulation resistance: 1000M Ω ;
 - 接触电阻 Contact resistance: 10m Ω ;
 - 防水等级 Waterproof: IP67;
 - 机械寿命 Mating cycles: 100 cycles;
 - 互配产品: ATP04-2P-XXXX (XXXX=所有扩展料号);
Mating part: ATP04-2P-XXXX (XXXX=A11 Extended Part);
 - 与产品互配的端子和线缆规格 Mating contacts and wire.

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE
12	3.35	4.20	10~14AWG

ITEM	PART NUMBER	Qty	DESCRIPTION	REMARK
MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED				
1) All dimensions are in metric(mm).				
2) Tolerances are as follows:				
1 PL DEC ± 0.30				
2 PL DEC ± 0.15 Fractions $\pm 1/64$				
3 PL DEC ± 0.08 Angles $\pm 1'$				
签名 SIGNATURE				
日期 DATE				
制图 DRAWN	JARRY		19/02/13	
审核 CHECKED	Oryow Li			
工艺 ENGINEER				
批准 APPROVAL	<i>Terry</i>		2013.02.22	
客户 CUSTOMER			244260-00600	
MATERIAL SPECIFICATIONS:				
SINE Systems Corporation				
A Subsidiary of Amphenol Corporation				
PROCESS SPECIFICATIONS:				
Assembly Connector Plug, 2 Way				
DWG NO: ATP06-2S-XXX				
第三角投影 第三角投影 THIRD ANGLE PROJECTION				
文件编号 文件编号 FILE NO.				
尺寸 尺寸 SIZE				
质量 质量 MASS				
版次 版次 REV.				
比例 比例 SCALE				
A3				
A2				
XX				
NEXT ASSY:				
SHEET 1 OF 1				