


Technische Daten

Specifications

Caractéristiques techniques

Dati tecnici

Modell Model Modèle Modello	Messbereich Measuring range Plage de mesure Campo di misura	Innenwiderstand Inside Resitance Résistance interne Resistenza interna
PM-2/30UA PM-2/50UA PM-2/+ -50UA PM-2/100UA	30 µA 50 µA ±50 µA 100 µA	6,5 kΩ 3,0 kΩ 1,9 kΩ 1,9 kΩ
PM-2/1MA PM-2/50MA PM-2/100MA	1 mA 50 mA 100 mA	200 Ω 1,2 Ω 0,65 Ω
PM-2/1A PM-2/3A PM-2/5A PM-2/10A PM-2/15A	1 A 3 A 5 A 10 A 15 A	60 mΩ 20 mΩ 12 mΩ 6 mΩ 4 mΩ
PM-2/10V PM-2/15V PM-2/25V PM-2/30V PM-2/300V/AC	10 V 15 V 25 V 30 V 300 V~	10 kΩ 15 kΩ 25 kΩ 30 kΩ 300 kΩ



Abmessungen in mm,
Toleranz ±0,2 mm

Dimensions in mm,
tolerance ±0.2 mm

Dimensions en mm,
tolérance ±0,2 mm

Dimensioni in mm,
tolleranza ±0,2 mm

Änderungen vorbehalten.

Subject to technical modification.

Tout droit de modification réservé.

Con la riserva di modifiche tecniche.