



MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
-----------------	-----------------	-----------------

120054-0045	BEYA03P-FBP-05	16.40' +6.50" -0 [5.0M +165.1mm -0]
-------------	----------------	-------------------------------------



FUNCTION	COLOR
+ V	BROWN
- V	BLUE

PORT (CONTACT #)	COLOR
PORT 1(2)	GREY/PINK
PORT 1(4)	WHITE
PORT 2(2)	RED/BLUE
PORT 2(4)	GREEN
PORT 3(2)	WHITE/GREEN
PORT 3(4)	YELLOW
PORT 4(2)	BROWN/GREEN
PORT 4(4)	GREY
PORT 5(2)	WHITE/YELLOW
PORT 5(4)	PINK
PORT 6(2)	YELLOW/BROWN
PORT 6(4)	RED
PORT 7(2)	WHITE/GREY
PORT 7(4)	BLACK
PORT 8(2)	GREY/BROWN
PORT 8(4)	VIOLET
PORT 9(2)	WHITE/PINK
PORT 9(4)	WHITE/BLUE
PORT 10(2)	PINK/BROWN
PORT 10(4)	BROWN/BLUE

BEYA03P-FBP-05

Wire type
2x.50mm + 20x.25mm
Black PUR

cable length
05----5 Meter
100----10 Meter

CONTACT:	GOLD/NICKEL OVER COPPER ALLOY
INSERT:	PUR, BLACK
HOUSING:	TPU, YELLOW
VOLTAGE RATING:	10 VAC/30 VDC
AMPERAGE RATING:	6 AMPS
PROTECTION:	IP67
OPERATING TEMPERATURE:	-5°C TO 90°C

INITIAL RELEASE EC NO.: IPG2014-0063 DRWN: EBRACKEN 2013/07/09 CHKD: RSTONE APPR: BWOODMAN 2013/08/16	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
	▽=0 ∇=0	mm INCH	IN/MM	---	INCH		
		4 PLACES ±--- ±--- 3 PLACES ±--- ±.005 2 PLACES ±0.13 ±.010 1 PLACE ±0.25 ±.020	DRAWN BY DATE EBRACKEN 2013/06/18	TITLE	M8-MPIS 4 POLE-10 PORT END-5M CABLE BLACK PUR		
		ANGULAR ±.5°	CHECKED BY DATE RSTONE	MOLEX INCORPORATED			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	APPROVED BY DATE BWOODMAN 2013/08/16	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-120054-003	SHEET NO. 1 OF 1		
			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			