

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
 © COPYRIGHT 2006 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS
 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECR-10-007266	22APR2010	HMR	T.M
C		REVISED PER ECR-14-001037	24JAN2014	K.T	N.Y

1. MATERIAL: HOUSING: LIQUID CRYSTAL POLYMER
 COLOR: BLACK
 CONTACT: COPPER ALLOY
 SOLDER PEG: BRASS

SCALE 1:1

2. FINISH (ALL OVER): NICKEL PLATING 1.27μm MIN

3. FINISH (CONTACT AREA): GOLD PLATING 0.76μm MIN AFTER 2

4. FINISH (SOLDER PEG & CONTACT TAIL): TIN PLATING 2μm MIN AFTER 2

5. COPLANARITY 0.15mm MAX. (CONTACT TINE AND SOLDER PEG ONLY)

6. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

7. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1. 材料: ハウジング: 液晶ポリマー、色: 黒
 コンタクト: 銅合金
 ソルダーペグ: 黄銅

2. めっき(全面): ニッケル下地めっき 1.27μm 以上

3. めっき(接触部): 2の上金めっき 0.76μm 以上

4. めっき(ソルダーペグとコンタクト半田付部): 2の上金めっき 2μm 以上

5. コンタクトタイン部及びソルダーペグの平面度(コプラナリティ)は 0.15mm MAX

6. 文字の形状、大きさ、および位置等は、大略を示すものであり詳細を示すものではありません。

7. Y KEY形状は、X KEY形状と左右対称

CONTACT TAB
 CONTACT TAIL
 40 POS (X-KEY): 1-1939995-0
 LOGO MARK
 KEYING
 CIRCUIT NO
 ROW ID BOTH SIDE
 SOLDER PEG
 HDR HSG

OUTLINE OF HDR HSG
 REFERENCE PC BOARD PATTERN: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
 参考基板取寸法: コネクタ搭載面 (非累積公差)

13.4 (HSG)
 SERIES CODE
 DATE CODE
 DETAIL A

DETAIL A SCALE 4:1
 DETAIL B SCALE 4:1
 0.1 REF (CONTACT/PEG)

0.76μm MIN	40	Y	19	38.0	43.2	48.6	48.44	21.6	2-1939995-0
0.76μm MIN	40	X	19	38.0	43.2	48.6	48.44	21.6	1-1939995-0
0.76μm MIN	26	Y	12	24.0	29.2	34.6	34.44	14.6	2-1939995-3
0.76μm MIN	26	X	12	24.0	29.2	34.6	34.44	14.6	1-1939995-3
0.38μm MIN	22	X	10	20.0	25.2	30.6	30.44	12.6	1-1939995-4
GOLD	POS	KEY	n	A	B	C	D	E	PART NO

Ø 1.5
 4.4
 CAVITY MARK (NUMERAL LETTER)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. MAEBASHI 06NOV2006
 CHK T. KUDO 06NOV2006
 APVD D. MITSUGI 06NOV2006

NAME 名称 DYNAMIC D1100D 2.0mm PITCH HDR ASSY, SMT/V-TYPE 22-40POS

PRODUCT SPEC 108-78414
 APPLICATION SPEC 114-5405

WEIGHT
 Customer Drawing

SCALE 2:1 SHEET 1 OF 2 REV C

1470-19 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006 BY -

ALL RIGHTS RESERVED.

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

Dimensions: C, B, $2Xn=A$, D REF (PEG)

26POS(X-KEY): I-1939995-3

Dimensions: C, B, $2Xn=A$, D REF (PEG)

22POS(X-KEY): I-1939995-4

Pin 13, Pin 1, D1100 logo

Pin 11, Pin 1, D1100 logo

Dimension E

Dimension E

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 概
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

一般公差
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-

MATERIAL
材料
TBD

FINISH
仕上
-

DWN 06NOV2006

M. MAEBASHI

CHK 06NOV2006

T. KUDO

APVD 06NOV2006

D. MITSUGI

PRODUCT SPEC

製品規格
108-78414

APPLICATION SPEC

取付適用規格
114-5405

WEIGHT

Customer Drawing

TE Connectivity

NAME
名称

DYNAMIC D1100D 2.0mmPITCH
HDR ASSY, SMT/V-TYPE
22-40POS

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

C-1939995

RESTRICTED TO
-

SCALE
尺度
2:1

SHEET
2 OF 2

REV
C

1470-19 (3/13)