



PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

INSULATOR: PBT
 FLAMMABILITY RATING: UL94-V0
 COLOR: BLACK
 CONTACT MATERIAL: PHOSPHOR BRONZE
 CONTACT TYPE: STAMPED
 CONTACT PLATING: SELECTIVE GOLD
 SHIELDING: BRONZE NI PLATED
 QUALITY CLASS: 500 MATING CYCLES

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 TO 85°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 1.5A
 WORKING VOLTAGE: 120VAC
 INSULATOR RESISTANCE: >1000 MΩ
 WITHSTANDING VOLTAGE: 1000 VAC/MIN
 CONTACT RESISTANCE: 20 mΩ MAX
 SYSTEM APPLICATION: CAT 5 COMPATIBLE

STANDARD
 CERTIFIED: E324776

SOLDERING:
 JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
 TRAY

RoHS Compliant

G			
F	17-JUL-14	CHARACTERISTICS	AS
E	03-JAN-14	UL & TEMP UPDATE	QL
D	20-AUG-13	DIM UPDATE	QL
C	05-JUL-12	DIM	GG
B	06-OCT-09	UL STANDARD	JP
A	06-NOV-07	PDF	EC
REV	DATE	FILE	BY

PROJECTION:	
APPROVAL: RJ	

TOLERANCES UNLESS OTHERWISE SPECIFIED
0~10 ± 0.1
10~20 ± 0.15
20~30 ± 0.2
UNIT: MM
SCALE:
SHEET: 1/1
DRAW:

DESCRIPTION: SHIELDED 3.05mm FRONT GROUNDING POST 8P8C MODULAR JACK TAB DOWN	SIZE A4
WERI PART NO: 615 008 140 121	