

## MECHANICAL DETAILS

**Shell Style Model** EP\* : Elbow receptacle for printed circuit


**Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

**Housing Material** PPS (Polyphenylene) shell, other pieces nickel plated brass

**Cable Fixing** 0 - 0 mm

**Variant 2** :

	A	D	H	I	K	L	N
Mm.	6.8	11.5	3.5	7	8.7	19	7.1
In.	0.27	0.45	0.14	0.28	0.34	0.75	0.28




## PERFORMANCE DETAIL

**Insert** 0.302 : 2 Low Voltage

**Insulator** L: PEEK

**Specifications**

**Contact Type:** Print (straight)




## OTHER CHARACTERISTICS

**Shell Style/Model** Libellé







**IP Rating** 50



## Available Download

 [unipole\\_multipole.pdf](#)

## Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)