

MECHANICAL DETAILS

Shell Style Model FG* : Straight plug cable collet


Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

Cable Fixing 2.8 - 3.5 mm

Variant 2 :

	A	L	M	S1	S2
Mm.	6.4	28.5	20.5	5.5	5
In.	0.25	1.12	0.81	0.22	0.20



Available Download

 [unipole_multipole.pdf](#)

PERFORMANCE DETAIL

Insert :

Insulator L: PEEK

Specifications

Contact Type: Solder

Max. Matings: 5000

Contact Dia.: 0.35 mm (0.01in)

Bucket Dia.: 0.4 mm (0.016in)

Max. Solid 0.09 mm² (AWG 28)

Max. Stranded 0.05 mm² (AWG 30)

R (max): 8.7 mOhm









OTHER CHARACTERISTICS

Shell Style/Model Libellé

IP Rating 50



Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)