

rotronic

Datenblatt - Fiche technique - Data sheet


11.99.8841




VALUE USB 2.0 Kabel, Typ A-B, 4,5m

VALUE Câble USB 2.0 Type A-B, 4.5m

VALUE USB 2.0 Cable, Type A-B, 4.5 m



PIN OUT



NOTE:

| ITEM NO | LENGTH |
|------------|--------|
| 11.99.8809 | 800mm |
| 11.99.8819 | 1800mm |
| 11.99.8831 | 3000mm |
| 11.99.8841 | 4500mm |

NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10M Ω;
 - Contact resistance:3 Ω Max;
 - Dielectric strength:100V AC/Minute, 1mA.
- RoHS & REACH compliant
- PRINTING:USB 2.0 CABLE, 28AWG×1P+28AWG×2C
- Packing: 1PCS/PE BAG + LABEL 100PCS/CARTON

MATERIAL LIST:

| | | | | |
|---|------------|--|---|--|
| ④ | OUTER MOLD | Shore 88A PVC(UL94V-2) Color: White | 2 | |
| ③ | USB B TYPE | USB B /M Type, The Pin Gold Plating 30U", the shell for Nickel Plating | 1 | |
| ② | USB A TYPE | USB A /M Type, The Pin Gold Plating 30U", the shell for Nickel Plating | 1 | |
| ① | CABLE | USB 2.0 28AWG(7/0.12BC*1P)+28AWG(7/0.12BC*2C)+AB B=0.12/3*16 AL-MG JACKET:PVC/WHITE OD: 4.0mm, Braid Coverage: 48% | 1 | |

| NO. | PARTS NAME | SPECIFICATION STANDARD | QT' Y | REMARK |
|-----|------------|-------------------------------|-------|--------|
| BY | CHK | REVISION RECORD MODIFICATIONS | DATE | REV. |

| Rotronic Co., Ltd. | | | | |
|--------------------|----------------------------|--------|------------|---------------|
| CUSTOMER | RT | REF. | ITEM NO. | See The Chart |
| PRODUCT NAME | VALUE USB 2.0 Cable, AM/BM | | UNTT | MM |
| DRAWNBY | CHECKBY | APPOBY | DATE | |
| Elaine | | | 2011-08-02 | |