

rotronic

Datenblatt - Fiche technique - Data sheet


11.99.8931




VALUE USB 2.0 Kabel, Typ A-A, 3,0m

VALUE Câble USB 2.0 Type A-A, 3.0m

VALUE USB 2.0 Cable, Type A-A, 3 m



PIN OUT



NOTE 1:

ITEM NO.	LENGTH
11. 99. 8909R	800 ± 20mm
11. 99. 8919R	1800 ± 30mm
11. 99. 8931R	3000 ± 50mm
11. 99. 8944R	4500 ± 100mm

NOTE:

1. Electrical test:
 - (1). 100% open short & miss wire test;
 - (2). Insulation resistance: DC 300V 10M Ω ;
 - (3). Contactor resistance: 3 Ω Max;
 - (4). Dielectric strength: 100V AC/Minute, 1mA.
 2. RoHS compliant
 3. PRINTING: USB 2.0 CABLE, 28AWG×1P+28AWG×2C
 4. Packing: 1PCS/PE BAG + LABEL 100PCS/CARTON
11. 99. 8909 50PCS/CARTON

MATERIAL LIST:

③	OUTER MOLD	Shore 88A PVC(UL94V-2) Color: White	2	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating 30U", the shell for Nickel Plating	2	
①	CABLE	USB 2.0 28AWG(7/0.12BC*1P)+28AWG(7/0.12BC*2C)+AB B=0.12/3*16 AL-MG JACKET:PVC/WHITE (WH11) OD: 3.8±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

Rotronic Co., Ltd

CUSTOMER		REF.		ITEM NO.	11. 99. 8909	11. 99. 8919
					11. 99. 8931	11. 99. 8944
PRODUCT NAME	USB 2.0 AM/AM		DRAW NO.		UNTT	MM
	DRAWNBY	CHECKBY	APPOBY	DATE		
BY	CHK	chenhuan	chenhuan	2009-11-20		

		NEW	2009-11-20	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.