

TOLERANCE UNLESS OTHERWISE
SPECIFIED IN MM:
0.0 ± 0.20 *ANGLE x*
0.00 ± 0.10
0.000 ± 0.05





THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

ORIGINAL

1



1. MATERIAL :

- 1-1 . HOUSING : LCP UL94V-0 ; COLOR : BLACK
- 1-2 . CONTACT : PHOSPHOR BRONZE
- 1-3 . SHELL : BRASS

2. PARTS

- 2-1 . EXTERNAL NUT : PBT UL 94V-0 ; COLOR : BLACK
- 2-2 . O-RING : EPDM (1.5*9.5) ; COLOR : BLACK.

3. PLATING

- 3-1 . CONTACT : GOLD PLATING ON CONTACT AREA
BRIGHT TIN ON SOLDER AREA
- 3-2 . SHELL : NICKEL PLATING ON OVER ALL

4. SPECIFICATION :

- 4-1. Water proof: IP67



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

WATERPROOF MINI USB TYPE B, 5P
(FEMALE)

ACAD REFERENCE NO.: 690-W05-260-044

DRAWN:R.STA.MONICA

DATE: MAY.01/2014

CHECKED:

DATE:

PART NUMBER

690-W05-260-044

SHEET 1 OF 1

DRAWING NUMBER

690-W05-260-044

ISSUE

1