


ECN MARK	ECN NO.	DESCRIPTION	DATE




- Drain wire: 5*30AWG(1/0.254mmBC)
- Conductor: 2C*30AWG(1/0.254mmBC)
- Insulation: HD-PE, OD: Ø0.5
- Conductor: 5*[30AWG(1/0.254mmBC)*1pair]
- Insulation: foamed-PE, OD: Ø0.7
- Insulator: 5*al
- Conductor: 30AWG(1/0.254mmBC)*1pair
- Insulation: HD-PE, OD: Ø0.5 HDPE(1 twisted)
- Lapping: AL/MY. 0.025*20mm
- Braiding: 128#/0.12ALMG+1/0.254mmBC
- Jackel: Ø7.3mm
- UL PVC, 70P. Black

**5P+4C(30AWG)
1.4 Version**

- FEATURES**
1. Gold-plated plugs
 2. compliant ROHS. 1080P

- ELECTRICAL SPECIFICATION:**
1. Withstanding voltage: 300VDC 0.1SEC
 2. Insulation Resistance: 5Mohm 300VDC

LENGTH
7500mm
5000mm
3000mm
2000mm
1000mm



5		DP Cable 5P+4C OD:7.3mm	IPC	
4		PVC BLACK	1PC	
3		PVC BLACK	1PC	
2		DP A PLUG 20PIN(Pins Gold-Plated, SHELL Gold-Plated)	1PC	
1		HDMI TYPE A PLUG 19PIN(Pins Gold-Plated, SHELL Gold-Plated)	1PC	
ITEM.	DWG NO	DESCRIPTIONS&SPECIFICATIONS	QTY.	REMARK

TOLERANCE	SIGNATURES	DATE	CPDPHD001	
20-99 ±20.00 100-999 ±30.0 1000-9999 ±50.00 10000-9999 ±100.00	DRAFT: Jay		SCALE	TITLE
	CHECKED: Neo			
	APPROVAL:		REV	A1
Unit:MM			DWG NO	