



| ECN MARK | ECN NO. | DESCRIPTION | DATE |
|----------|---------|-------------|------|
|          |         |             |      |



**5P+4C(30AWG)  
1.4 Version**


**FEATURES**

1. Gold-plated plugs
2. compliant ROHS. 1080P

**ELECTRICAL SPECIFICATION:**

1. Withstanding voltage: 300VDC 0.1SEC
2. Insulation Resistance: 5Mohm 300VDC

| LENGTH |
|--------|
| 7500mm |
| 5000mm |
| 3000mm |
| 2000mm |
| 1000mm |



| ITEM. | DWG NO | DESCRIPTIONS&SPECIFICATIONS                          | QTY. | REMARK | TOLERANCE                                                               | SIGNATURES   | DATE | CPDP002 |        |
|-------|--------|------------------------------------------------------|------|--------|-------------------------------------------------------------------------|--------------|------|---------|--------|
| 5     |        | DP Cable 5P+4C OD:7.3mm Silver                       | 1PC  |        | 20-99 ±20.00<br>100-999 ±30.0<br>1000-9999 ±50.00<br>10000-9999 ±100.00 | DRAFT: Jay   |      | SCALE   | TITLE  |
| 4     |        | METAL SHELL Zn ALLOY SHINING Silver                  | 1PC  |        |                                                                         | CHECKED: Neo |      |         |        |
| 3     |        | DP METAL SHELL Zn ALLOY SHINING Silver               | 1PC  |        |                                                                         | APPROVAL:    |      |         |        |
| 2     |        | DP A PLUG 20PIN(Pins Gold-Plated, SHELL Gold-Plated) | 1PC  |        |                                                                         |              |      |         |        |
| 1     |        | DP A PLUG 20PIN(Pins Gold-Plated, SHELL Gold-Plated) | 1PC  |        |                                                                         |              |      |         |        |
| ITEM. | DWG NO | DESCRIPTIONS&SPECIFICATIONS                          | QTY. | REMARK | Unit:MM                                                                 |              | REV  | A1      | DWG NO |