




ECN MARK	ECN NO.	DESCRIPTION	DATE



### 7P+5C(30AWG)

(1/0.23BC\*1P+1/0.23BC+AL+MY)\*7P+  
 1/0.23BC\*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG  
 PVC Jacket



### 7P+5C(28AWG)

28+30# OD8.6  
 (1/0.32BC\*1P+1/0.23BC+AL+MY)\*7P+  
 1/0.23BC\*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG  
 PVC Jacket

LENGTH	AWG
10000mm	28AWG OD:8.6
7500mm	28AWG OD:8.6
5000mm	30AWG OD:7.3
3000mm	30AWG OD:7.3
2000mm	30AWG OD:7.3
1000mm	30AWG OD:7.3

NO.	DWG NO	DESCRIPTIONS&SPECIFICATIONS	QTY.	REMARK	TOLERANCE	SIGNATURES	DATE	CPDVI002		
5		PVC BLACK	2PC		20-99 ±20.00 100-999 ±30.00 1000-9999 ±50.00 10000-9999 ±100.00	DRAFT: Jay		SCALE	TITLE	
4		Screw	4PC			CHECKED: Neo				
3		DVI Male 24+1PIN Gold plated	1PC			APPROVAL: James				
2		DVI Male 24+1PIN Gold plated	1PC							
1		PVC BLACK	1PC							
NO.	DWG NO	DESCRIPTIONS&SPECIFICATIONS	QTY.	REMARK	Unit:MM		REV	A1	DWG NO	