

DVI-D Dual link cable, Aluminium

CABLE POWER



ECN MARK	ECN NO.	DESCRIPTION	DATE

7P+5C(30AWG)
 (1/0.23BC*1P+1/0.23BC+AL+MY)*7P+
 1/0.23BC*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG
 PVC Jacket

7P+5C(28AWG)
 28+30# OD8.6
 (1/0.32BC*1P+1/0.23BC+AL+MY)*7P+
 1/0.23BC*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG
 PVC Jacket

LENGTH	AWG
10000mm	28AWG OD:8.6
7500mm	28AWG OD:8.6
6000mm	28AWG OD:8.6
5000mm	30AWG OD:8.6
4000mm	30AWG OD:8.6
3000mm	30AWG OD:8.6
2000mm	30AWG OD:8.6
1500mm	30AWG OD:8.6
1000mm	30AWG OD:8.6
500mm	30AWG OD:8.6

NO.	DWG NO	DESCRIPTION&SPECIFICATIONS	QTY.	REMARK
5		AL Metal Shell	2PC	
4		Screw	4PC	
3		DVI Male 24+1PIN Gold plated	1PC	
2		DVI Male 24+1PIN Gold plated	1PC	
1		PVC BLACK	1PC	

TOLERANCE	SIGNATURES	DATE	CPDVI003		
20-99 ±20.00 100-999 ±30.00 1000-9999 ±50.00 10000-9999 ±100.00	DRAFT: Jay		SCALE	TITLE	
	CHECKED: Neo				
	APPROVAL: James		REV	A1	DWG NO

Cable Power Ltd, 6 Brook House, Wivenhoe Business Centre,
 Wivenhoe, Essex, CO7 9DP

www.cablepower.co.uk +44 (0) 1206 825381