



ECN MARK	ECN NO.	DESCRIPTION	DATE



**1.4 Version**  
**5P+4C(30AWG)**

**FEATURES**

- 1. Gold-plated plugs
- 2. compliant ROHS.1080P

**ELECTRICAL SPECIFICATION:**

- 1. Withstanding voltage: 300VDC 0.1SEC
- 2. Insulation Resistance: 5Mohm 300VDC

LENGTH
1500mm
1000mm
500mm

Type A PIN	Signal Assignment	Type A PIN
1 Blue	Blue	1 Blue
2 ground	ground	2 ground
3 white	white	3 white
4 Blue	Blue	4 Blue
5 ground	ground	5 ground
6 white	white	6 white
7 Blue	Blue	7 Blue
8 ground	ground	8 ground
9 white	white	9 white
10 Blue	Blue	10 Blue
11 ground	ground	11 ground
12 white	white	12 white
14 Blue	Blue	14 Blue
17 ground	ground	17 ground
19 white	white	19 white
15 Yellow	Yellow	15 Yellow
16 Oreger	Oreger	16 Oreger
13 white	white	13 white
18 red	red	18 red
SHELL	SHELL	SHELL

ITEM.	DWG NO	DESCRIPTIONS&SPECIFICATIONS	QTY.	REMARK	TOLERANCE	SIGNATURES	DATE	CPHD007	
5		HDMI Cable 1.4V OD:6.0mm BLACK	1PC		20-99 ±20.00 100-999 ±30.00 1000-9999 ±50.00 10000-9999 ±100.00	DRAFT: Jay  CHECKED: Neo  APPROVAL: Zing		SCALE	TITLE
4		PVC BLACK 50P	1PC						
3		PVC BLACK 50P	1PC						
2		HDMI TYPE A PLUG 19PIN(Pins, SHELL Gold-Plated)	1PC						
1		HDMI TYPE A female	1PC						
Unit:MM						REV	A1	DWG NO	