


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6792: UPDATED LOGO, DRW FORMAT, PACKAGING, ADDED PANTONE #	4/10/13	D. DESJARDIN



MODEL NUMBER	LENGTH	
	FEET	METERS
DK238MF-3	3.0	0.91
DK238MF-6	6.0	1.83
DK238MF-10	10.0	3.05
DK238MF-15	15.0	4.57
DK238MF-20	20.0	6.10
DK238MF-25	25.0	7.62

WIRING MAP		
"J1"	COLOR	"P1"
1	LT. BLUE	1
2	LT. GREEN	2
3	PURPLE	3
4	WHITE	4
5	ORANGE	5
6	YELLOW	6
7	BROWN	7
8	RED	8
SHELL	DRAIN	SHELL

- NOTES:
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - E CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY TJC CHECKED BY RC APPROVED BY AFC	DATE 07/19/2000 07/19/2000 07/19/2000	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY I/O PRODUCTS
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. DK238MF		REV. E	SCALE: NONE CAD FILE: DK238MF.SLDDRW SHEET 1 OF 1