





| | | | | | | | |
|-----|------|-----------|-----|---------------|---------|-----|------|
| LOC | DIST | REVISIONS | | | | | |
| AI | 00 | P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | | D | | ECR-14-012060 | 11AUG14 | LS | GS |



- 1. HEXAGON SOCKET SCREW KEY 2.5 IS FIXED AT HAND TOOL
- 2. INSTRUCTION SHEET IS IN SCOPE OF DELIVERY
TE P/N 5-744001-2
- 3. PACKED IN ONE BOX
- OPTION
- 4. REPAIR KIT, TE P/N 539635-2
CONSISTING OF:
 10 DIE RETAINING SCREW, M4x11
 11 DIE RETAINING SCREW, M4x10
 12 ADJUSTMENT WHEEL
 13 RETAINING PLATE 4
 14 SCREWED STOP PIN, M3x5
 15 TENSION SPRING



| SPARE PARTS | | | | |
|-------------|-----|-----|------------|---------------------------|
| POS | QTY | REV | TE- P/N | DESCRIPTION |
| 2 | 1 | A | 519151-9 | Linsenkopfschraube, M4x10 |
| 3 | 1 | A | 8-539634-5 | Linsenkopfschraube, M4x11 |

| | | | | | |
|---|--|---------------------------------|---------|--|------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN D. Reissig | 28JAN99 | TE Connectivity | |
| DIMENSIONS: mm | | CHK U. Reuter | 03FEB99 | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± | | APVD U. Reuter | 03FEB99 | NAME ERGOCRIMP HAND TOOL ERGOCRIMP Handzange | |
| MATERIAL | | FINISH | | PRODUCT SPEC | RESTRICTED TO |
| | | Gewicht / Weight in Kg 0.626 | | APPLICATION SPEC | SIZE A3 |
| | | CUSTOMER DRAWING | | SCALE 1:1.5 | DRAWING NO 539635-1 |
| | | | | SHEET 1 OF 1 | REV D |