


A standard in-line 4mm banana plug with a stainless steel contact spring.
 The large rear diameter of this plug will accept cables with a conductor of up 5,5mm (10 awg).
 The lead wire is held by soldering in a large solder bucket.

The product is also supplied with a large diameter insulating cover that accepts cables with a maximum outside diameter of 7,1mm. Nickel plating Plug Body.

Material	
Contact spring	Stainless steel, BS302
Plug body	Brass TR1 CZ 131
Plug housing	Acetal, C 27021 R
Body plating	Silver plating
Rating	16 Amps
Voltage	50 Volts MAX

Dimensions



Part No.	Colour & Plug Plating	
579-0100	BLACK	(Silver Plated)
579-0200	BLUE	(Silver Plated)
579-0300	BROWN	(Silver Plated)
579-0400	GREEN	(Silver Plated)
579-0500	RED	(Silver Plated)
579-0600	WHITE	(Silver Plated)
579-0700	YELLOW	(Silver Plated)

Tel No. +44(0)1724 273200 Website www.dem-uk.com



PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ALPHA 3 MANUFACTURING.
 ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ALPHA 3 MANUFACTURING IS PROHIBITED.

DEM
 DEM Manufacturing, Deltron Emcon House
 Hargreaves Way, Sawcliffe Ind. Park,
 Scunthorpe, North Lincolnshire, DN15 8RF, UK

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETRES
 LINEAR TOLERANCE:
NO DECIMAL PLACES ±0.5mm
1 DECIMAL PLACE ±0.25mm
2 DECIMAL PLACES ±0.125mm
 ANGULAR TOLERANCE: ±1°

FINISH STANDARD 4MM PLUG SPB
 DEBURR AND BREAK SHARP EDGES
 IF IN DOUBT ASK DO NOT SCALE DRAWING
 MATERIAL SEE TABLE

DRAWN BY WC
 APPROVED BY SEE NOTE
 THIRD ANGLE PROJECTION
 SHEET 1 OF 1
 SCALE 1:1
 A4

TITLE GENERAL SPECIFICATION 579 SERIES PLUG
 DRAWING NO. 579 SERIES
 ISSUE **02**
 Release