

A range of high quality UK manufactured phono plugs made from machined brass with various plating options.


- Centre contact available in hollow tube.
- Ground contact with unique 'T' shape slot for maximum contact area.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification.
- Attractive body styling.
- Maximum cable size 5.5mm

Rating –

Rated Current: 5A.

Rated Voltage: 50V

Insulation resistance – 100M Ω at 500 Vdc



Material

- Centre contact :Brass, flash gold plated
- Ground contact :Brass, flash gold plated
- Insulation :Noryl SE1
- Cable clamp :Brass, flash gold plated
- Spring :Spring steel, flash gold plated
- Cap :Brass, flash gold plated

Deltron Part No.	Description
331-0000	FLASH GOLD PLATED
331-0100	FLASH GOLD PLATED (BLACK ID RING)
331-0200	FLASH GOLD PLATED (BLUE ID RING)
331-0500	FLASH GOLD PLATED (RED ID RING)
331-0600	FLASH GOLD PLATED (WHITE ID RING)
331-0700	FLASH GOLD PLATED (YELLOW ID RING)

Tel No. +44(0)1724 273200 Website www.dem-uk.com

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
 ALPHA 3 MANUFACTURING.
 ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF
 ALPHA 3 MANUFACTURING IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETRES
 LINEAR TOLERANCE:
NO DECIMAL PLACES $\pm 0.5\text{mm}$
1 DECIMAL PLACE $\pm 0.25\text{mm}$
2 DECIMAL PLACES $\pm 0.125\text{mm}$
 ANGULAR TOLERANCE: $\pm 1^\circ$



DEM Manufacturing, Deltron Emcon House
 Hargreaves Way, Sawcliffe Ind. Park,
 Scunthorpe, North Lincolnshire, DN15 8RF, UK

FINISH PROFESSIONAL PHONO LINE PLUG
 DEBURR AND BREAK SHARP EDGES
 IF IN DOUBT ASK
 DO NOT SCALE DRAWING
 MATERIAL SEE NOTE

DRAWN BY SPB
 APPROVED BY WC
 THIRD ANGLE PROJECTION

SHEET 1 OF 1
 SCALE 1:1
 A4

TITLE GENERAL SPECIFICATION
 331 SERIES
 PHONO LINE PLUG
 DRAWING NO. 331 SERIES
 ISSUE 03
 Release