



Datenblatt - Fiche technique - Data sheet

11.02.8818




ROLINE USB 2.0 Kabel, Typ A-B, 1,8m


ROLINE Câble USB 2.0, Type A-B, 1.8m

ROLINE USB 2.0 Cable, A - B, M/M, 1.8 m

RoHS Compliant



WIRE ADDRESS



Electrical Test:
 1.100% TEST OPEN SHORT MIS-WIRE.
 2.CONTACT RESISTANCE:3Ω MAX.
 3.INSULATION RESISTANCE:5MΩ MIN.
 4.HI-POT:300V DC/10MS.

D		
C	Delete 2.0 VER LOGO	2016.04.29
B	Remove the stickers on the line	2016.01.06
VER.A	REVISE	DATE

NUMBER	PRODUCT SPECIFICATIONS	Quantity	Unit
4	45P PVC BLACK		G
3	USB 2.0 B MALE(White Insulator, Nickel Plated,Contact Gold Plated 30U")	1	PCS
2	USB 2.0 A MALE(White Insulator, Nickel Plated,Contact Gold Plated 30U")	1	PCS
1	UL2725 28AWG*1P+24AWG*2C+AB(BC),OD=5.0mm,BLACK PVC JACKET.	1	PCS

Item	11.02.8818	
Draw	Sam	Date: 2015.03.26
Approval		
Duty	F16	

SECOMP