




Datenblatt - Fiche technique - Data sheet


11.02.9020



ROLINE USB 2.0 Kabel, C-Micro B, ST/ST, 1m

ROLINE Câble USB 2.0, C-Micro B, M/M, 1m

ROLINE USB 2.0 Cable, C – Micro B, M/M, 1m



P/N	Length
11.02.9020	1000 ± 30 mm
11.02.9021	2000 ± 30 mm


NOTE:

1. USB 2.0 Cable 28AWG*2P+24AWG*2C OD:4.2±0.2mm Color: Black
2. USB Micro B Solder Type Shell Nickel White Insulation
3. USB C M Solder Type Shell Nickel, Black Insulation
4. INSIDE MOLDING:PE
5. OUTSIDE MOLDING:Black PVC

Electrical Test:

1. 100%Test(Open, short, miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 5M ohm min.
4. Hi-pot:300V DC/10ms

Pin Assignment



REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DRAWING	DESIGN	DRAWING NAME	ROLINE USB 2.0 Cable, Type C - Micro B M/M, black	
				RANGE	Pla	Met	Ina	Por	Cab	Pac	Gas						DIS	DATE
△				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	PHILIP	PHILIP	HENRY	2015-08-28	11.02.9020, 11.02.9021	
△				6~30	0.1	0.1	.15	.25	1	1	0.5	.25						
△				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3						
△				80~180	.15	.15	.25	0.3	2	2	1	.45						
△				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6						
△				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1	SCALE	1:1	UNIT	MM		