



Datenblatt - Fiche technique - Data sheet

11.04.5785



ROLINE DisplayPort Kabel DP - UHDTV, ST/ST, schwarz, 1,0 m



ROLINE Câble DisplayPort DP - UHDTV, M/M, noir, 1,0 m

ROLINE DisplayPort Cable, DP - UHDTV, M/M, black, 1.0 m

RoHS Compliant

P1

HDMI MALE



DISPLAYPORT PLUG

P2

Pin Assignment


Test requirement:

Resolution: 4K*2K@60HZ

Table :

P/N	Length
11.04.5785	1000 ± 20 mm
11.04.5786	2000 ± 30 mm
11.04.5787	3000 ± 40 mm

- 1 Cable [30AWG(7/0.1T)x1P+D+AL+MYLAR]x5P+30AWG(7/0.1T)x5C+F+ADB16/5/0.12(AL) ◦
Jacket : PVC, Black ◦ O.D.=6.0±0.20mm ◦
- 2 DP Connector Male, Solder, Gold Plated ◦
- 3 Clip DP
- 4 Shell DP : ABS, Black
- 5 HDMI Connector DP to HDMI PCB'A, Gold Plated
Shell : ABS, Black
- 6 PE LDPE
- 7 PVC 60P, Black



REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DRAWING	DESIGN	DRAWING NAME	ROLINE DisplayPort Cable, DP-UHDTV, M/M		
				RANGE	Pla	Met	Ins	Por	Cab	Pac	Gas						DIS	DATE	PART NO.
①				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	PHILP	PHILP	TREE	2016-05-6	PART NO.	11.04.5785, 11.04.5786, 11.04.5787	ROO
②				6~30	0.1	0.1	.15	.25	1	1	0.5	.25							
③				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3							
④				80~180	.15	.15	.25	0.3	2	2	1	.45							
⑤				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6							
				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1	SCALE	1:1	UNIT	MM			