



<b>ITEM-NO. (ITEM-NO.)</b>	2092-1404
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	16
<b>RM (PIN SPACING / mm)</b>	5
<b>P (NO. OF POLES)</b>	4
<b>Height (Height / mm)</b>	19.5
<b>Width (Width / mm)</b>	22.2
<b>Depth (Depth / mm)</b>	14.4
<b>COLOR (COLOR)</b>	lichtgrau
<b>Comment (Comment)</b>	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 7.2 \text{ mm}$
<b>Dimensions (Dimensions)</b>	1.6 +0.1 mm