



ITEM-NO. (ITEM-NO.)	284-601
Cross section1 (Cross section / mm²)	0.2 - 10
Cross section2 (Cross section / AWG)	24 - 08
Strip length (Strip length / mm)	12 - 13
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	57
Height (Height / mm)	33.5
Width (Width / mm)	10
Depth (Depth / mm)	69
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	19.1
Comment (Comment)	