



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
L	ECN 8473 :UPD DWG TO MATCH NEW DESIGN , ADD MATERIAL&NOTE7 INFO	09/02/16	D.CUI
M	ECN 8516:UPD NOTES 4&5,CANCELED NOTES 3	10/20/16	D.CUI



(.46 MIN.)
[11.75]



PART NUMBER	LENGTH	
	METER	FEET
WPUSBAX-05M	0.5	1.64
WPUSBAX-1M	1.0	3.28
WPUSBAX-2M	2.0	6.56
WPUSBAX-3M	3.0	9.84
WPUSBAX-5M	5.0	16.41

- NOTES:**
1. THESE CABLE ASSEMBLIES ARE CONSTRUCTED TO MEET THE REQUIREMENTS OF THE UNIVERSAL SERIAL BUS SPECIFICATION USB 2.0
 2. CONNECTOR CONTACTS HAVE 30 μINCHES GOLD PLATING OVER NICKEL PLATING
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
 4. L-COM LOGO STYLE AND MOLDED HOOD APPEARANCE MAY VARY PER L-COM SPECIFICATION
 5. INGRESS PROTECTION RATING IS IP67 (J1 ONLY ,MATED)
 6. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031


REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2[51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%
 ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ±.2 [5.08]
 .XX = ±.02 [5.1]
 .XXX = ±.005 [1.3]

APPROVALS	DATE
DRAWN BY C.MCCORMICK	07/29/2003
CHECKED BY D.PARHAM	07/29/2003
APPROVED BY R.CARRICK	07/29/2003

L-com Global Connectivity
 50 HIGH STREET
 NORTH ANDOVER, MA
 01845

CATEGORY: USB
 PRODUCT DESCRIPTION: USB WATERPROOF SERIES "A" BULKHEAD TO SERIES "A" PLUG



SIZE	FSCM NO.	DWG. NO.	REV.
B	43321	WPUSBAX	M