


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO
C	ECN 4303: ADDED PACKAGING NOTE FOR PS-0031	10/5/09	D.FRISIELLO



NOTES:

1. RECOMMENDED CABLE DIAMETER: 0.138 ϕ THRU 0.276 ϕ
2. IP (INGRESS PROTECTION) RATING: 67.
3. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

MATERIALS:

GASKETS: EPDM
 BODY: NYLON
 HOUSING: ABS
 O-RING: SILICONE
 SEAL: EPDM
 SEALING NUT: NYLON
 THUMBSCREW: BRASS

FINISH:

THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = \pm .1 .XX = \pm .02 .XXX = \pm .005 ANGULAR TOLERANCES: ALL = \pm 1°	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY C.MCCORMICK	01/28/2004	
	CHECKED BY D.PARHAM	01/28/2004	
	APPROVED BY R.CARRICK	01/28/2004	CATEGORY DATA CABLING
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION HD15 FEMALE WATERPROOF CONNECTOR	
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. WPHDB15S-KIT	REV. C
		SCALE: NONE	CAD FILE: WPHDB15S-KIT.SLDDRW
			SHEET 1 OF 1