





**END AND INTERMEDIATE PLATE 4  
MM / 0.157 IN THICK**  
282-316

<b>ITEM-NO. (ITEM-NO.)</b>	282-316
<b>Height (Height / mm)</b>	31.5
<b>Width (Width / mm)</b>	4
<b>Depth (Depth / mm)</b>	62
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	4.89