





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|--|---------|-------------|
| REV | DESCRIPTION | DATE | APPROVED |
| E | ECN 6554: REVISED DIM TO [1.4], ROHS, FORMAT, REMOVE FINISH, MAT'L PC TO ABS | 2/12/14 | D.FRISIELLO |
| F | ECN 8260: REMOVED L-COM LOGO FROM REAR HOUSING | 2/18/16 | D.FRISIELLO |
| | | | |



| WIRING MAP | |
|------------|------|
| "J1" | "J2" |
| 1 | 1 |
| 2 | 2 |
| 3 | 3 |
| 4 | 4 |
| 5 | 5 |
| 6 | 6 |
| 7 | 7 |
| 8 | 8 |



NOTES:

MATERIAL:
 HOUSING: ABS, UL94V-0, COLOR: IVORY
 CONTACTS: PHOSPHOR BRONZE
 CONTACT PLATING: GOLD, 30 μ INCHES OVER NICKEL PLATING.

ELECTRICAL:
 CURRENT RATING: 2 AMPS (MAX.)
 VOLTAGE RATING: 140 VDC

MISCELLANEOUS:
 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.
 OPERATING TEMPERATURE RANGE: -20 °C TO +80 °C.
 RATING APPLICATION: CATEGORY 3

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

| | | | | |
|--|--------------------------------------|-------------------------------|---|-----------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3] | APPROVALS DRAWN BY D.FRISIELLO | DATE 4/23/12 | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| | CHECKED BY D.DESJARDIN | 4/23/12 | | CATEGORY TELECOM/MODULAR |
| | APPROVED BY D.GALLAGHER | 4/23/12 | PRODUCT DESCRIPTION CPLR PNL MNT 8X8K STRAIGHT IVY | SIZE A |
| | PROJECTION | COLOR VARIATIONS MAY OCCUR | FSCM NO. 43321 | DWG. NO. ECF504-8SK |
| SCALE: NONE | | CAD FILE: ECF504-8SK.SLDDRW | | |
| SHEET 1 OF 1 | | | REV. F | |