



<b>ITEM-NO. (ITEM-NO.)</b>	770-104
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.5 - 4
<b>Cross section2 (Cross section / AWG)</b>	20 - 12
<b>Strip length (Strip length / mm)</b>	9
<b>Measured voltage (Measured voltage / V)</b>	400
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	25
<b>P (NO. OF POLES)</b>	4
<b>Height (Height / mm)</b>	17
<b>Width (Width / mm)</b>	44.6
<b>Depth (Depth / mm)</b>	75.9
<b>No. of connection Points (No. of connection Points)</b>	8
<b>No. of potentials (No. of potentials)</b>	4
<b>COLOR (COLOR)</b>	schwarz
<b>WEIGHT (WEIGHT / g)</b>	24.712