



ITEM-NO. (ITEM-NO.)	770-124
Cross section1 (Cross section / mm²)	0.5 - 4
Cross section2 (Cross section / AWG)	20 - 12
Strip length (Strip length / mm)	9
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	25
P (NO. OF POLES)	4
Height (Height / mm)	17
Width (Width / mm)	44.6
Depth (Depth / mm)	75.9
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	4
COLOR (COLOR)	weiß
WEIGHT (WEIGHT / g)	24.712