



ITEM-NO. (ITEM-NO.)	745-503/006-000
Cross section1 (Cross section / mm²)	0.2 - 16
Cross section2 (Cross section / AWG)	24 - 06
Strip length (Strip length / mm)	12 - 13
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	76
RM (PIN SPACING / mm)	10
P (NO. OF POLES)	3
Height (Height / mm)	27
Width (Width / mm)	31
Depth (Depth / mm)	33
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	27
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 10 mm L1 = L + 1,7 mm
Dimensions (Dimensions)	2,2 + 0,1 mm