



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/09/2017	B.ZHANG

"P1"




2X, HDMI MALE
19 PIN CONNECTOR
GOLD PLATED CONTACTS






2X, OVERMOLDED HOOD,
PVC, RED(PANTONE 193C)

UL STYLE 20276, HIGH FLEX HDMI CABLE
(5) INDIVIDUALLY SHIELDED TWISTED PAIRS, 28AWG, WITH DRAIN WIRE,
(4) INDIVIDUAL CONDUCTORS, 28AWG,
OVERALL SHIELD: ALUMINUM MYLAR PLUS BRAIDED TINNED COPPER,
OUTER JACKET: PVC, BLACK



WIRE MAP



PART NUMBER	LENGTH	
	METERS	FEET
VHA00001-05M	0.5	1.64
VHA00001-1M	1	3.28
VHA00001-2M	2	6.56
VHA00001-3M	3	9.84

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031. THE PACKAGE IS TO INCLUDE A STICKER THAT SAYS "HDMI HIGH SPEED WITH ETHERNET" PER THE HDMI LICENSING, LLC GUIDELINES. THE STICKER WILL BE CENTERED DIRECTLY UNDER THE L-COM LABEL.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY B.ZHANG	05/04/2017		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY B.GATES	05/06/2017	PRODUCT DESCRIPTION	
	APPROVED BY S.PAN	05/06/2017	CA HDMI M-M, HI-FLEX	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
SCALE: NONE		CAD FILE: VHA00001.SLDDRW	DWG. NO. VHA00001	REV. A
SHEET 1 OF 1				