



注記
NOTES

- 1.適合ハウジング : 5046963,505605 SERIES
APPLICABLE HOUSING:5046963,505605 SERIES
- 2.材料 MATERIAL
銅同衾(t=0.2)
COPPER ALLOY
錫めっき 0.7μm以上 リフロー処理(前めっき)
TIN 0.7μm以上 REFLOW TREATMENT(PRE-TINNED)
- 3.△トレードマーク : MXプラス1文字の製造工場を示す
アルファベットにて表示。
但し"J"はJAPANを示す。
FORMED BY MX AND 1 MORE LETTER OF ALPHABET
WHICH MEAN THE MANUFACTORY.
BUT "J" MEANS JAPAN. (TO TRADE MARK) (ex MXJ)
ELV AND RoHS COMPLIANT
- 4.適用電線サイズ AWG#18 ~ 22
APPLICABLE WIRE AWG#18 ~ 22
- 5.被覆外径 : 1.55 ~ 2.6mm
INSULATION OUTSIDE DIAMETER : 1.55 ~ 2.6mm
- 6.製品仕様書及び取り扱いについては、製品仕様書
5056050000PS000、コネクタ取扱説明書 5056050000PSA00,A01
を参照願います。
PLEASE REFER TO PRODUCTS SPECIFICATION
5056050000PS000 AND USER'S MANUAL 5056050000PSA00,A01.
- 7.圧着仕様書については、圧着仕様書 5056070000PSC00を参照
願います。
PLEASE REFER TO CRIMPING SPECIFICATION
5056070000PSC00.
- 8.ATS-57427-0000 圧着視覚教材を参照願います。
PLEASE REFER TO CRIMPING VISUAL ATS-57427-0000.

PLASTIC BAG	5056070100	バラ状 LOOSE
REEL	5056070000	連鎖状 CHAIN
PACKAGING SPEC.	オーダー番号 ORDER NO.	形態 FORM
CONNECTOR SERIES NO. 505607-0*00		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
EC NO: 118591 DRWN: NITO CHK'D: SAKIYAMA APPR: TKANEKO	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	
	ANGULAR TOL ± 3.0 °		MM	10:1	
	4 PLACES ± 0.2	DRWN BY	DATE		
	3 PLACES ± 0.2	NITO	2017/05/19		
	2 PLACES ± 0.2	CHK'D BY	DATE		
	1 PLACE ± 0.2	SAKIYAMA	2017/06/19		
0 PLACES ± 0.2	APPR BY	DATE			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		TKANEKO	2017/06/16		
C	REV	DRAWING SIZE	THIRD ANGLE PROJECTION		PRODUCT CUSTOMER DRAWING SERIES: 505607 MATERIAL NUMBER: SEE CHART CUSTOMER: GENERAL DOCUMENT NUMBER: 5056070000 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 1 OF 1
		A3			