


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. ** (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1M-86	.13 (3.3)	.87 (22)	.044 (1.1)	.098 (2.5)	.159 (4.0)	.186 (4.7)	.188 (4.8)	3.9 (100)	18 (80)	MINIATURE	CURVED	.07 (34)
PLT2I-86	.13 (3.3)	2.00 (51)	.047 (1.2)	.135 (3.4)	.200 (5.1)	.180 (4.6)	.240 (6.1)	8.0 (203)	30 (134)	INTERMEDIATE	CURVED	.21 (96)
PLT2S-86	.13 (3.3)	1.85 (47)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.30 (186)	50 (222)	STANDARD	CURVED	.35 (157)
PLT3S-86	.13 (3.3)	3.00 (76)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	11.50 (291)	50 (222)	STANDARD	CURVED	.56 (252)
PLT4S-86	.13 (3.3)	4.00 (102)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	14.40 (366)	50 (222)	STANDARD	CURVED	.71 (324)
PLT3H-86	.25 (6.4)	3.00 (76)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	11.10 (282)	120 (534)	LIGHT-HEAVY	STRAIGHT	1.15 (522)
PLT4H-86	.25 (6.4)	4.00 (102)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	14.40 (366)	120 (534)	LIGHT-HEAVY	STRAIGHT	1.42 (643)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

2) COMPOSED OF METAL DETECTABLE NYLON.

3) MATERIAL FLAMMABILITY: CONFORMS TO UL94V-HB.

**4) CONDITIONED FOR 24 HRS @ 120° F/20% RH.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

						TITLE PAN-TY CABLE TIES - PLT METAL DETECTABLE SERIES						
						CONTROL DRAWING						
						ITEM REVISION NAME W10001BF/03						
						DATASET FILE NAME W10001BF/03-SS-27556						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± ---- .xxx ± .020 (.51) .xx ± .02 (.5) ANGLES ± ----						
						MATERIAL: METAL DETECTABLE NYLON - COLOR: BLUE						
						DRAWING NUMBER: SS-27556						
03	9/20/16	BWG	MPH	JADE	UPDATED TITLE BORDER AND NOTE 1. SEE ECN DOCUMENT FOR COMPLETE DETAILS.	010688/00						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY ERW	DATE 5/29/07	CHK TGS	SCALE NONE	SHT 1 OF 1	SIZE A

D10100DA/20