


**450-3326 Solder mount socket, for .059 (1,52) to .062 (1,57) diameter pins**

Recommended mounting hole .102 (2,59) ± .002 (0,05), #38 drill



Min hole depth .200 (5,08)

**How to order code**

**450-3326-01-XX-00**

**Basic Part No XX = Finish**

MATERIALS				
Component	Material	Finish(-03)	Finish(-04)	Finish(-06)
Body	Brass	Gold over Nickel	Tin	Tin
Spring	Beryllium copper	Gold over Nickel	Tin	Gold over Nickel



Dimensions in inches [mm]

Tolerance unless otherwise stated  $\pm 0.005$  [0.13]