


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER ECO-16-010988	22JUL2016	JPS	JLM
D		REVISED PER ECO-17-013859	20SEP2017	CR	JLM



NOTES: UNLESS OTHERWISE SPECIFIED.

1. SILKSCREEN TE LOGO, TE PN, REVISION LETTER ON TOP LAYER. FOLLOWED BY 4 DIGIT DATE CODE.
2. MATERIAL: FR4, COPPER THICKNESS 1 OZ, TOTAL THICKNESS 0.304 WITH OUT ADHESIVE.
3. FINISH: ENIG-ELECTROLESS NICKEL IMMERSION GOLD ON EXPOSED SOLDER AREAS PRIOR TO SOLDERING.
4. PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY ENVIROMENTAL SPECIFICATION TEC-138-702.
5. ADHESIVE; REMOVE PAPER BACKING OF PRESSURE SENSITIVE ADHESIVE TO APPLY.
6. REFERENCE TE DATASHEET DS2118059-1 FOR ANTENNA SPECIFICS.

150.00	2118059-3
NON-SALABLE	2118059-2
350.00	2118059-1
A	PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J. SCHOLZ	22 JUL 2016	TE Connectivity	
DIMENSIONS:		CHK	J. SCHOLZ	22 JUL 2016		
mm		APVD	J. MOORE	22 JUL 2016		
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± FINISH -		NAME WMAX SINGLE BAND, U.FL CABLE 2300 Mhz-3800<Mhz		
MATERIAL	-	PRODUCT SPEC	-		SIZE	A2
	-	APPLICATION SPEC	-		CAGE CODE	-
	-	WEIGHT	-		DRAWING NO	G-2118059
	-	CUSTOMER DRAWING	SCALE 4:1		SHEET 1 OF 1	REV D