



Datenblatt - Fiche technique - Data sheet

11.04.5210




ROLINE VGA-Kabel HD15 ST - ST, 10,0m

ROLINE Câble HD15 M/HD15 M, 10,0m

ROLINE HQ VGA Cable HD15, M/M, 10 m

ROHS-COMPLIANT


LTR	REV.	DESCRIPTION	DATE



NOTE:

- CABLE: UL-2919 28AWG(7/0.127 T.C)*3COAX(75 OHMS)
+24AWG(7/0.203 T.C)*7C+AL/MY+D.W+BRAID(85%)
PVC JACKET; COLOR:BLACK(NK-K01) OD: $\varnothing 8.5 \pm 0.15$ mm, (C2919356-1)
- CONNECTOR:
P1&P2:HDB15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL
(THE 9TH PIN UNLOAD)
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD: MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
- ELECTRICAL TEST: <1>.100% OPEN SHORT & MIS WIRE TEST
<2>.CONTACT RESISTANCE 3 Ohms MAX
<3>.INSULATION RESISTANCE 10M Ohms MIN
- PACKING: EACH PC / POLYBAG + BAR CODE LABEL.

120-3212-4	11.04.5250	50000±500	2	7611990111626
120-3212-3	11.04.5230	30000±300	2	7611990111619
120-3212-2	11.04.5220	20000±200	2	7611990111602
120-3212-1	11.04.5210	10000±100	5	7611990111596
DWG	P/N	L±T(mm)	PCS/CTN	BAR CODE NO.



Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Drawn
FANNIE 11/18/09'

Check

Engr

Rotronic Co., LTD.
Title: HDB15/M - HDB15/M CABLE
Customer P/N

App'd

Scale NONE Units m/m Third Angle Projection

Dwg No. 120-3212 REV:A Sheet 1/1