

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:  
 INSULATION MATERIAL: PC  
 RATED VOLTAGE: 830V  
 RATED CURRENT: 40A  
 INSULATION RESISTANCE:  $\geq 400M\Omega$   
 RATED IMPULSE VOLTAGE: 8KV  
 POLLUTION DEGREE: 3  
 FLAMMABILITY: UL94V-0  
 MATING CYCLES: 500 CYCLES  
 WIRE RANGE:  $1.0mm^2 \sim 6.0mm^2$   
 CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.  
 (ORDER No. REFER TO DRAWING: T20400X10XX000)

注释:

1. 技术参数:  
 绝缘材料: PC  
 额定电压: 830V  
 额定电流: 40A  
 绝缘电阻:  $\geq 400M\Omega$   
 脉冲电压: 8KV  
 污染等级: 3  
 阻燃等级: UL94V-0  
 插拔次数: 500次  
 接线范围:  $1.0mm^2 \sim 6.0mm^2$   
 接线类型: 冷压接

2. 端子需要单独订购。  
 (订货号参考图面: T20400X10XX000)

T2111042101-007	HMN-004-M	HMN-004 MALE MODULE INSERT HMN-004 模块公插
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC $\pm$
	1 PLC $\pm$
	2 PLC $\pm$
	3 PLC $\pm$
	4 PLC $\pm$
	ANGLES $\pm$
MATERIAL	FINISH
-	-
-	-

DWN	19SEP2017
YORK CHEN	
CHK	19SEP2017
GINO YAO	
APVD	19SEP2017
CHRIS WANG	
PRODUCT SPEC	108-137060
APPLICATION SPEC	114-137060
WEIGHT	-
CUSTOMER DRAWING	

		NAME		RESTRICTED TO
		HMN-004-M		
SIZE	CAGE CODE	DRAWING NO	-	
A3	00779	T2111042101007	-	
SCALE		SHEET	OF	REV
3:2		1	1	B

1470-19 (3/13)