

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW
	B1	ECR-18-013580	30AUG2018	WQR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:  
 INSULATION MATERIAL: PC  
 RATED VOLTAGE: 50V  
 RATED CURRENT: 5A  
 INSULATION RESISTANCE:  $\geq 400M\Omega$   
 RATED IMPULSE VOLTAGE: 0.8KV  
 POLLUTION DEGREE: 3  
 FLAMMABILITY: UL94V-0  
 MATING CYCLES: 500 CYCLES  
 WIRE RANGE: 0.08~0.52 mm<sup>2</sup> (28~20 AWG)  
 CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.  
 (ORDER No. REFER TO DRAWING: T20700X20XX000)

注释:

1. 技术参数:  
 绝缘材料: PC  
 额定电压: 50V  
 额定电流: 5A  
 绝缘电阻:  $\geq 400M\Omega$   
 额定脉冲电压: 0.8KV  
 污染等级: 3  
 阻燃等级: UL94V-0  
 插拔次数: 500次  
 接线范围: 0.08~0.52 mm<sup>2</sup> (28~20 AWG)  
 接线类型: 冷压接

2. 端子需要单独订购.  
 (订货号参考图面: T20700X20XX000)

T2111092201-007	HMN-009-F	HMN-009 FEMALE MODULE INSERT HMN-009 模块母插
PART NUMBER 料号	PART DESCRIPTION 描述	
DWN YORK CHEN 19SEP2017 CHK GINO YAO 19SEP2017 APVD CHRIS WANG 19SEP2017 PRODUCT SPEC 108-137064 APPLICATION SPEC 114-137064 WEIGHT -		NAME HMN-009-F SIZE A3 CAGE CODE 00779 DRAWING NO. T2111092201007 RESTRICTED TO -
CUSTOMER DRAWING		SCALE 3:2 SHEET 1 OF 1 REV B1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL -	FINISH -

1470-19 (3/13)